

**LED headlamp, Type: H7R.2****Order data**

Order number	081486 H7R.2
GTIN	4029113729802
Item class	04B

Description**Version:**

Powerful high-quality LED headlamps **Power illumination**, can be steplessly focussed and dimmed. With several illumination modes.

Rechargeable. With Li-ion battery and USB charger.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Attention:

German version. Order free UK adapter plug No. 08 1174_GB.

Technical description

Including belt pocket	no
Illumination range	50 - 160 m
Battery voltage	3.7 V
Illumination time	4 - 30 h
Advanced Focus System (AFS)	yes
Illumination	20 - 300 lm
Weight	165 g

Manufacturer's designation	H7R.2
Power supply	Mains operated
Smart Light Technology (SLT)	yes
Battery capacity	1.4 Ah
Head Ø	35 mm
Rapid Focus	yes
IP Index of Protection	IP X6
ATEX zone	no
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Dimmable lighting	yes
Type of product	Headlamp