

Garant GRIDLINE

ESD drawer 50 kg, 26×24G, Drawer front height: 100mm**Order data**

Order number	972454 100
GTIN	4069515000208
Item class	9GK

Description**Version:**

100% full extension drawers with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Light grey similar to RAL 7035, **ESD powder-coated**.

Technical description

Usable width	650 mm
Weight	15 kg
Usable depth in G	24
Usable depth	600 mm
Application range	Tool cabinet
Front height	100 mm
Usable width in G	26
Drawer/pull-out shelf load capacity	50 kg
Drawer usable area in G	26×24

Data sheet

Usable height	75 mm
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Drawer