

Garant GRIDLINE

ESD drawer 50 kg, 26×24G, Drawer front height: 125mm**Order data**

Order number	972454 125
GTIN	4069515000215
Item class	9GK

Description**Version:**

100% full extension drawers with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Light grey similar to RAL 7035, **ESD powder-coated.**

Technical description

Usable height	100 mm
Usable width	650 mm
Usable width in G	26
Application range	Tool cabinet
Weight	15 kg
Usable depth in G	24
Drawer usable area in G	26×24
Drawer/pull-out shelf load capacity	50 kg
Front height	125 mm

Data sheet

Usable depth	600 mm
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Drawer