

Garant GRIDLINE

ESD drawer, 36×24G, Drawer front height: 125mm



Order data

Order number	972474 125
GTIN	4069515000338
Item class	9GK

Description

Version:

100% full extension drawers with differential runners.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body and fronts light grey similar to RAL 7035 **ESD powder-coated**.

Technical description

Usable width	900 mm
Usable depth in G	24
Front height	125 mm
Weight	19 kg
Drawer/pull-out shelf load capacity	50 kg
Usable depth	600 mm
Usable height	100 mm
Drawer usable area in G	36×24
Usable width in G	36
with individual drawer release system	no

Data sheet

Application range	Tool cabinet
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer