

Garant GRIDLINE

**ESD drawer with one-hand individual drawer release system 50 kg, 26×24G,
Drawer front height: 50mm****Order data**

| | |
|--------------|---------------|
| Order number | 972456 50 |
| GTIN | 4069515000246 |
| Item class | 9GK |

Description**Version:**

100% full extension drawers with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

With **one-hand individual drawer release system** – prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Light grey similar to RAL 7035, **ESD powder-coated**.

Technical description

| | |
|---------------------------------------|--------------|
| Drawer/pull-out shelf load capacity | 50 kg |
| Drawer usable area in G | 26×24 |
| Usable depth | 600 mm |
| Usable depth in G | 24 |
| with individual drawer release system | yes |
| Usable width in G | 26 |
| Usable height | 25 mm |
| Application range | Tool cabinet |

Data sheet

| | |
|--|----------|
| Front height | 50 mm |
| Weight | 11 kg |
| Usable width | 650 mm |
| Individual drawer release system | One-hand |
| Drawer runner extension (partial/full extension) | 100 % |
| electrostatic characteristic | EGB/ESD |
| Drawer usable width × usable depth in G | 26×24G |
| Type of product | Drawer |