

Garant GRIDLINE

**ESD drawer with one-hand individual drawer release system 50 kg, 26×24G,
Drawer front height: 200mm****Order data**

Order number	972456 200
GTIN	4069515000291
Item class	9GK

Description**Version:**

100% full extension drawers with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

With **one-hand individual drawer release system** – prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Light grey similar to RAL 7035, **ESD powder-coated**.

Technical description

Usable height	175 mm
Drawer usable area in G	26×24
Drawer/pull-out shelf load capacity	50 kg
Usable width	650 mm
Usable depth	600 mm
Front height	200 mm
Application range	Tool cabinet

Data sheet

Usable depth in G	24
with individual drawer release system	yes
Individual drawer release system	One-hand
Usable width in G	26
Weight	18 kg
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Drawer