

Garant GRIDLINE

ESD drawer, 36×24G, Drawer front height: 50mm**Order data**

Order number	972474 50
GTIN	4069515000307
Item class	9GK

Description**Version:****100% full extension drawers** with differential runners.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:Drawer body and fronts light grey similar to RAL 7035 **ESD powder-coated.****Technical description**

Usable width in G	36
Drawer/pull-out shelf load capacity	50 kg
Application range	Tool cabinet
Usable depth in G	24
Front height	50 mm
Usable depth	600 mm
Usable width	900 mm
Drawer usable area in G	36×24
Usable height	25 mm
with individual drawer release system	no

Data sheet

Weight	14 kg
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer