

Garant GRIDLINE

ESD drawer, 36×24G, Drawer front height: 200mm**Order data**

Order number	972474 200
GTIN	4069515000352
Item class	9GK

Description**Version:****100% full extension drawers** with differential runners.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:Drawer body and fronts light grey similar to RAL 7035 **ESD powder-coated**.**Technical description**

Drawer/pull-out shelf load capacity	50 kg
Weight	22 kg
with individual drawer release system	no
Application range	Tool cabinet
Front height	200 mm
Usable height	175 mm
Usable width in G	36
Usable width	900 mm
Usable depth in G	24

Data sheet

Drawer usable area in G	36×24
Usable depth	600 mm
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer