

Garant GRIDLINE

**ESD drawer, 36×24G, Drawer front height: 75mm****Order data**

Order number	972474 75
GTIN	4069515000314
Item class	9GK

**Description****Version:**

**100% full extension drawers** with differential runners.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

**Supplied with:**

Drawers each complete with 1 pair drawer runner rails.

**Colour:**

Drawer body and fronts light grey similar to RAL 7035 **ESD powder-coated**.

**Technical description**

Usable width	900 mm
Usable width in G	36
with individual drawer release system	no
Front height	75 mm
Application range	Tool cabinet
Usable depth	600 mm
Usable height	50 mm
Drawer/pull-out shelf load capacity	50 kg
Drawer usable area in G	36×24
Weight	16 kg

## Data sheet

Usable depth in G	24
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer