



Electrical angle grinder with kick-back stop, for 180 mm discs Ø, with adjustable grasp handle, with restart inhibit, Type: 27-180JR



Order data

Order number	077146 27-180JR
GTIN	4053423252484
Item class	03C

Description

Version:

Powerful 180 mm angle grinder:

- Powerful 2700 W motor with soft start and starting current limiter.
- High protection of the user by vibration control on the main and auxiliary handles, kick-back stop and restart inhibit.
- Bow handle rotates 90° for optimum grinding and cutting.

Supplied with:

Includes quick-adjustable safety guard, additional handle, two-pin wrench, mounting flange, clamping nut. In a box.

Technical description

Special features	Rotatable loop handle
Kick-back stop	yes
maximum vibration to EN	5.5 m/s ²
Height	139 mm

Cable length	4 m
Restart block	yes
maximum speed	6900 - 8500 min ⁻¹
Power consumption	2700 W
Manufacturer's designation	GWS 27-180JR
Soft start	yes
Toolholder	M14
Power supply	Mains operated
Packaging	cardboard
maximum disc Ø	180 mm
Width	310 mm
maximum cutting depth	35 mm
Length	530 mm
Weight	6.1 kg
Type of product	Angle grinder