



## KOMET Reamax® TS holder Plain shank, long, for reaming head Ø D: 20-21,99mm



### Order data

Order number	239890 20-21,99
GTIN	4047109229358
Item class	27E

### Description

#### Suitable for :

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

#### Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.

Please order a hexagon key L-wrench separately if required.

Through-coolant: yes

Overhang A: 140 mm

Overall length  $L_{tot}$ : 190 mm

Shank length  $L_s$ : 50 mm

Shank Ø  $D_s$  h6: 20 mm

Pull stud No. 239900: 2

Wrench No. 239901: 5AF

### Technical description

for reaming head Ø D	20 - 21.99 mm
Activation wrench No. 239902	2.5AF (2.5Nm)
Pull stud No. 239900	2
Shank length $L_s$	50 mm
Overhang A	140 mm
Overall length $L_{tot}$	190 mm
Wrench No. 239901	5AF
Shank Ø $D_s$ h6	20 mm

Shank type	long
Through-coolant	yes
Type of product	Phillips bit

---

## Accessories

Pull stud Type 2	239900 2
Wrench for pull studs Drive SW5	239901 SW5