

 KOMET

KOMET Reamax® TS holder DAH® Zero Plain shank, short, for reaming head Ø D: 22-26,99mm

Order data

Order number	239930 22-26,99
GTIN	
Item class	27E

Description
Version:

The holder is pre-loaded and set to < 0.005 mm run-out. For run-out accuracies to precision < 3 µm, longer tool life, and higher process reliability.

Suitable for:

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.
Please order a hexagon key L-wrench separately if required.

Technical description

Shank length L _s	50 mm
Pull stud No. 239900	3
for reaming head Ø D	22 - 26.99 mm
Overall length L _{tot}	145 mm
Activation wrench No. 239902	3AF (4Nm)
Overhang A	80 mm
Wrench No. 239901	SW6
Shank Ø D _s h6	20 mm
Shank type	short
Through-coolant	yes

Type of product

Phillips bit

Accessories

Pull stud Type 3

239900 3

Wrench for pull studs Drive SW6

239901 SW6