

Garant GRIDLINE

Perforated panel upright cabinet width 30G with Plain sheet metal swing doors, Height: 2000mm



Order data

Order number	942111 2000
GTIN	4069515001021
Item class	9GI

Description

Version:

Perforated panel upright cabinets with pull-out panels and swing doors, reinforced on the inside and can be locked by 2-component Haptoprene® slide handle with a cylinder lock. With free-standing vertical pull-out frames, with □ 9×9mm at 37 mm intervals for mounting GARANT easyFix hooks and holders, and perforated panel accessories. Perforated panels adjustable on a 25-mm grid. The perforated panels are arranged as telescopic sections. Load capacity per pull-out frame 80 kg.

Cabinet with central subdivision, with □ 9×9mm at 37 mm intervals for mounting GARANT easyFix hooks and holders. Usable area for each side of the vertical pull-out frame is 1.54 m².

Colour:

Standard body and pull-out frames RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For suitable accessories such as GARANT easyFix hooks and holders see Group 95.

No additional perforated panel pull-out frames can be installed.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth in G	20
Weight	116 kg
Depth	500 mm
Height	2000 mm
Width in G	30
Width	750 mm
Version	Perforated panel vertical cabinet
Vertical pull-out frame usable depth	456 mm
Vertical pull-out frame usable height	1692 mm
Vertical pull-out frame load capacity	80 kg
Number of shelves	5
Number of pull-out frames	1
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Cabinet housing internal load capacity	1000 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Upright cabinet

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/942111-2000>