

Garant GRIDLINE

Perforated panel upright cabinet width 40G with Plain sheet metal swing doors, Height: 2000mm



Order data

Order number	942151 2000
GTIN	4069515001083
Item class	9GI

Description

Version:

Perforated panel upright cabinets with pull-out panels and swing doors, reinforced on the inside and can be locked by 2-component Haptoprene® slide handle with a cylinder lock. With free-standing vertical pull-out frames, with □ 9×9mm at 37 mm intervals for mounting GARANT easyFix hooks and holders, and perforated panel accessories. Perforated panels adjustable on a 25-mm grid. The perforated panels are arranged as telescopic sections. Load capacity per pull-out frame 80 kg.

Usable area of both sides per vertical pull-out frame 2.2 m². **With single pull-out protection.**

Colour:

Standard ex stock – body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For suitable accessories such as GARANT easyFix hooks and holders see Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	1000 mm
-------	---------

Data sheet

Depth in G	28
Version	Perforated panel vertical cabinet
Height	2000 mm
Width in G	40
Vertical pull-out frame usable height	1692 mm
Vertical pull-out frame usable depth	656 mm
Depth	700 mm
Vertical pull-out frame load capacity	80 kg
Weight	186 kg
Number of pull-out frames	3
Cabinet housing internal load capacity	1000 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Upright cabinet

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/942151-2000>