



KOMET Reamax® TS holder Plain shank, long, for reaming head Ø D: 22-26,99mm



Order data

Order number	239890 22-26,99
GTIN	
Item class	27E

Description

Suitable for:

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.
Please order a hexagon key L-wrench separately if required.

Technical description

Shank length L _s	50 mm
Overall length L _{tot}	210 mm
Wrench No. 239901	SW6
for reaming head Ø D	22 - 26.99 mm
Activation wrench No. 239902	3AF (4Nm)
Pull stud No. 239900	3
Overhang A	160 mm
Shank Ø D _s h6	20 mm
Shank type	long
Through-coolant	yes
Type of product	Phillips bit

Accessories

Pull stud Type 3	239900 3
Wrench for pull studs Drive SW6	239901 SW6