



## KOMET Reamax® TS holder Plain shank, short, for reaming head Ø D: 18-19,99mm



### Order data

Order number	239880 18-19,99
GTIN	4047109229310
Item class	27E

### Description

#### Suitable for :

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

#### Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.

Please order a hexagon key L-wrench separately if required.

Through-coolant: yes

Overhang A: 80 mm

Overall length  $L_{tot}$ : 130 mm

Shank length  $L_s$ : 50 mm

Shank Ø  $D_s$  h6: 20 mm

Pull stud No. 239900: 1

Wrench No. 239901: 5AF

### Technical description

Activation wrench No. 239902	8IP (1.5Nm)
Overhang A	80 mm
Overall length $L_{tot}$	130 mm
for reaming head Ø D	18 - 19.99 mm
Pull stud No. 239900	1
Shank length $L_s$	50 mm
Wrench No. 239901	5AF

Shank $\varnothing$ D <sub>s</sub> h6	20 mm
Shank type	short
Through-coolant	yes
Type of product	Phillips bit

---

## Accessories

Pull stud Type 1	239900 1
Wrench for pull studs Drive SW5	239901 SW5