



## KOMET Reamax® TS holder Plain shank, long, for reaming head Ø D: 35-41,99mm



### Order data

Order number	239890 35-41,99
GTIN	4047109280120
Item class	27E

### Description

#### Suitable for :

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

#### Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.

Please order a hexagon key L-wrench separately if required.

Through-coolant: yes

Overhang A: 200 mm

Overall length  $L_{tot}$ : 256 mm

Shank length  $L_s$ : 56 mm

Shank Ø  $D_s$  h6: 25 mm

Pull stud No. 239900: 5

Wrench No. 239901: 10AF

### Technical description

Overall length $L_{tot}$	256 mm
Activation wrench No. 239902	3AF (6Nm)
Shank length $L_s$	56 mm
for reaming head Ø D	35 - 41.99 mm
Pull stud No. 239900	5
Overhang A	200 mm
Wrench No. 239901	10AF
Shank Ø $D_s$ h6	25 mm

Shank type	long
Through-coolant	yes
Type of product	Phillips bit

---

## Accessories

Wrench for pull studs Drive SW10	239901 SW10
Pull stud Type 5	239900 5