



KOMET Reamax® TS holder DAH® Zero Plain shank, long, for reaming head Ø D: 18-19,99mm



Order data

Order number	239940 18-19,99
GTIN	
Item class	27E

Description

Version:

The holder is pre-loaded and set to < 0.005 mm run-out. For run-out accuracies to precision < 3 µm, longer tool life, and higher process reliability.

Suitable for:

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.
Please order a hexagon key L-wrench separately if required.

Technical description

Overhang A	140 mm
Shank length L _s	50 mm
Activation wrench No. 239902	8IP (1.5Nm)
Overall length L _{tot}	205 mm
Pull stud No. 239900	1
Wrench No. 239901	5AF
for reaming head Ø D	18 - 19.99 mm
Shank Ø D _s h6	20 mm
Shank type	long
Through-coolant	yes
Type of product	Phillips bit

Accessories

Wrench for pull studs Drive SW5

239901 SW5

Pull stud Type 1

239900 1