



KOMET Reamax® TS holder Plain shank, long, for reaming head Ø D: 42-51,99mm



Order data

Order number	239890 42-51,99
GTIN	
Item class	27E

Description

Suitable for:

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.
Please order a hexagon key L-wrench separately if required.

Technical description

Pull stud No. 239900	5
Overhang A	220 mm
Activation wrench No. 239902	4AF (10Nm)
Wrench No. 239901	10AF
for reaming head Ø D	42 - 51.99 mm
Shank length L _s	60 mm
Overall length L _{tot}	280 mm
Shank Ø D _s h6	32 mm
Shank type	long
Through-coolant	yes
Type of product	Phillips bit

Accessories

Wrench for pull studs Drive SW10

239901 SW10

Pull stud Type 5

239900 5