

**HOLEX®**
**CNMG 120408 Set 10 pieces, Grade: HBX130**

**Order data**

Order number	250252 HBX130
GTIN	4045197661548
Item class	22D

**Description**

CNMG 120408 Set of 10 pieces HBX130 Grade: HBX130

Chip breaker: MM

Cutting depth  $a_p$ : 1 - 6 mm

Feed  $f$ : 0.05 - 0.55 mm/rev.

Cutting speed  $v_c$  main application: 60 - 200 m/min

**Technical description**

Corner radius	0.8 mm
Main application	M
Cutting speed $v_c$ main application	60 - 200 m/min
Cutting depth $a_p$	1 - 6 mm
Cutting conditions	slightly interrupted
Chip breaker	MM
Feed $f$	0.05 - 0.55 mm/rev.

Grade	HBX130
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CNMG 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning