



Value pack cordless drill/driver



Order data

Order number	GG0210 M18BLDDRC2
GTIN	
Item class	GGN

Description

Version:

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use.

Supplied with:

Supplied in each case with 2 pcs. M18 Red-Li-ion rechargeable batteries, M12-18 FC charger, belt clip, HD box (carrying case).

3 pcs. cordless drill/driver No. 070210 size M18BLDDRC2.

Note:

See No. 073816, No. 073827 and No. 073840 ff. for suitable replacement batteries and chargers.

Technical description

Manufacturer's designation	M18 BLDDRC-202C
Quick-clamping chuck range	1.5 - 15 mm

Packaging	Modular case (HD=Heavy Duty)
Motor design	Brushless motor
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
typical application	Strong
maximum vibration to EN	<2.5 m/s ²
maximum speed 1st speed	0 - 550 min ⁻¹
maximum twist drill size Ø in steel	13 mm
Number of rechargeable batteries contained	2
maximum torque hard	60 Nm
Battery voltage	18 V
Power supply	Battery-powered
maximum speed 2nd speed	1700 min ⁻¹
Battery capacity	2 Ah
maximum twist drill size Ø in wood	52 mm
Type of rechargeable battery	Lithium-ion
Weight	1.5 kg
Type of product	Drill/driver
USP1	Cordless drill/driver

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG0210-M18BLDDRC2>