



Cordless jigsaw, Type: M18FBJS-5



Order data

Order number	GG8211 M18FBJS-5
GTIN	
Item class	GGN

Description

Version:

Sturdy general-purpose jig-saws with metal gearbox casings and overload protection. On/Off switch

can be operated by either hand, thus allowing use in many different positions.

With **FIXTEC quick-release clamping system** allows blades to be changed in seconds without any tools, and **selectable orbital stroke** for optimum cutting power and dust extraction combined with reduced saw blade wear.

Cordless jigsaw, brushless POWERSTATE™ motor for high cutting power. Switch for 6 speed settings, with soft start. LED illumination of the working area.

Supplied with:

Supplied in each case with 1 pc. charger, 2 pcs. 18 V / 5 Ah Li-ion rechargeable battery, 1 pc. saw blade, adapter for dust extraction, dust cover, plastic sliding shoe and HD box.

Supplied with chip break guard. 2 pcs. cordless jigsaw No. 078211 size M18FBJS-5.

Note:

Suitable spare batteries and chargers can be found under No. 073808 – 073840.

See No. 588400 – 588551 for jigsaw blades.

Technical description

Data sheet

Number of rechargeable batteries contained	2
Battery capacity	5 Ah
Manufacturer's designation	M18FBJS-502X
maximum sawn thickness steel	10 mm
Mitre angle adjustment	yes
Battery voltage	18 V
Special features	general purpose use
tool change without tools	yes, FIXTEC system
Weight	28 kg
maximum vibration to EN	6.3 m/s ²
Orbital stroke	5-fold
maximum sawn thickness wood	100 mm
Format	Straight handle
Type of rechargeable battery	Lithium-ion
Power supply	Battery-powered
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Rate of strokes	800 - 3500 min ⁻¹
Packaging	Carrying case
Type of product	Saw
USP1	Cordless jigsaw

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG8211-M18FBJS-5>