



Value pack cordless charger



Order data

Order number	GG3840 M1218FC
GTIN	
Item class	GGN

Description

Version:

Chip-controlled impulse charge technology. With battery charge display and overload protection.

The batteries are charged successively in sequence as they have been inserted.

- **Red, continuous light: The battery is being charged.**
- **Red, slow flashing: Battery in waiting mode.**
- **Green, continuous light: Battery charged.**

Quick charger for batteries with 12, 14, and 18 V Li-ion technology.

Charger 18 V/2.0 Ah battery in 26 min, 18 V/5 Ah in 59 min.

Supplied with:

4 pcs. battery charger No. 073840 size M1218FC.

Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Manufacturer's designation	M12-18 FC
Type of product	Charger

USP1

Rechargeable battery charger

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG3840-M1218FC>
