



Cordless impact wrench / driver, Type: GDS18450HC



Order data

Order number	GG4052 GDS18450HC
GTIN	
Item class	GGN

Description

Version:

Cordless impact wrench / impact driver.

· **Reversible.**

· **Battery charge display.**

1/2-inch impact wrench with Bluetooth® connectivity.

· **2 operating modes for metal and wood. Further parameters can be set individually using the Toolbox app.**

Supplied with:

Supplied in each case with 2 pcs. Li-ion rechargeable batteries, charger, L-BOXX. 3 pcs. cordless impact wrench/driver No. 074052 size GDS18450HC.

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Technical description

No load speed	1000 min ⁻¹
Number of impacts 2nd stage	2500 min ⁻¹
maximum break-away torque	800 Nm

Data sheet

Weight without battery	16 kg
Number of impacts 3rd stage	3300 min ⁻¹
Battery voltage	18 V
Number of impacts	0 - 3300 min ⁻¹
Number of rechargeable batteries contained	2
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum torque hard	450 Nm
Tool arbor size	1/2" in
maximum vibration to EN	145 m/s ²
maximum speed 1st speed	1500 min ⁻¹
Tool arbor drive profile	External square drive
maximum speed 2nd speed	2300 min ⁻¹
Manufacturer's designation	GDS 18V-450 HC
Power supply	Battery-powered
Number of impacts 1st stage	1900 min ⁻¹
Battery capacity	4 Ah
Type of rechargeable battery	Lithium-ion
Weight	21 kg
maximum torque 3rd step	450 Nm
maximum torque 2nd step	330 Nm
Packaging	Modular case (L-Boxx)
typical application	Heavy Duty
maximum screw Ø (8.8 - 12.9)	M20
maximum torque 1st step	250 Nm
Type of product	Impact wrench

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG4052-GDS18450HC>