



ER mini collet holder cylindrical, for ER collet size: 8



Order data

Order number	300681 8
GTIN	4069515001434
Item class	32A

Description

Version:

Through hole for internal cooling provided.

Optional extras:

ER collets No. 308878 – 309434, Spare ER nuts No. 309580; 309650.

Note:

Not suitable for shrink processes. No length adjustment available.

Technical description

Shank length L_1	200 mm
External $\varnothing D$	12 mm
for ER collets	8 mm
L_2	15.6 mm
Clamping range	0.5 - 5 mm
Shank $\varnothing d$	12 mm
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Collet chuck

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/300681-8>
