

**ER mini collet holder cylindrical, for ER collet size: 16****Order data**

Order number	300681 16
GTIN	4069515001458
Item class	32A

Description**Version:**

Through hole for internal cooling provided.

Optional extras:

ER collets No. 308878 – 309434, Spare ER nuts No. 309580; 309650.

Note:

Not suitable for shrink processes.

Technical description

Shank Ø d	20 mm
Clamping range	0.5 - 10 mm
for ER collets	16 mm
External Ø D	22 mm
L ₂	27.5 mm
Shank length L ₁	200 mm
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/300681-16>
