

Garant

BMT boring bar toolholder, BMT: 65-72



Order data

Order number	319888 65-72
GTIN	4069515001472
Item class	31V

Description

Version:

For internal and external cooling.

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

Suitable for efficient cooling systems such as GARANT eco, but also for other systems. Optimised outer contour.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball injection nozzles up to 80 bar.**

Application:

Internal and external machining in CNC lathes with BMT tool turrets.

For internal machining with boring bar holder or indexable drills.

Suitable for:

CNC lathes with BMT tool turret.

Note:

Other BMT holders with different sizes and dimensions are available on request.

Technical description

x	72 mm
L ₂	70 mm
L ₁	73 mm
L ₃	40 mm
h ₁	96 mm
l ₁	106 mm
Z	77 mm
d _a	40 mm
Type of product	Steel toolholder