



LED cordless floodlight, Power consumption: 20



Order data

Order number	081208 20
GTIN	4069515011235
Item class	02A

Description

Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**

COB-LED work light with frosted glass lens for homogeneous and pleasant illumination.

Supplied with:

Including battery charger.

Technical description

Overall length	196 mm
Overall height	226 mm
Overall width	68 mm
Type of rechargeable battery	Lithium-ion
Illumination	1100 - 2200 lm
Power supply	Battery-powered

Data sheet

Bulb	LED lamp
IP Index of Protection	IP 65
Power consumption	20 W
Type of product	Floodlight