



Pro Eco lever lock toolholder PWLNR 95°, for indexable inserts PW.., right



Order data

Order number	251924 20/08
GTIN	4069515004046
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

ISO code toolholder	PWLNR/L 2020K08
Lever screw	259019 1
Shim	259034 3
Head length L ₁	32 mm
Series	Pro Eco
suitable indexable insert	WN.. 0804..
Lever	259016 1
Overall length L	125 mm
Functional width L ₄	25 mm
Standard	Works standard
Shank size	2 mm
Insert size	8 mm

Pin	259045 1
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/251924-20/08>