



Pro Eco lever lock toolholder PCLNL 95°, for indexable inserts PC.., left



Order data

Order number	250045 25/12
GTIN	4069515004077
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Shank size	25 mm
Overall length L	150 mm
Head length L ₁	26 mm
Lever screw	259019 1
Shim	259034 1
suitable indexable insert	CN.. 1204..
ISO code toolholder	PCLNR/L 2525M12
Functional width L ₄	32 mm
Insert size	12 mm
Lever	259016 1
Standard	Works standard
Series	Pro Eco

Pin	259045 1
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250045-25/12>