



Pro Eco lever lock toolholder PWLNL 95°, for indexable inserts PW.., left



Order data

Order number	251925 20/08
GTIN	4069515004107
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Lever	259016 1
Insert size	8 mm
Lever screw	259019 1
Shim	259034 3
suitable indexable insert	WN.. 0804..
Head length L ₁	32 mm
Overall length L	125 mm
Shank size	20 mm
Functional width L ₄	25 mm
Series	Pro Eco
ISO code toolholder	PWLNR/L 2020K08
Standard	Works standard

Pin	259045 1
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/251925-20/08>