



Steel boring bar A... SSSCR 75°, for indexable inserts SC.., right



Order data

Order number	260722 16/09
GTIN	4069515004473
Item class	21T

Technical description

Insert size	9 mm
Set of insert screws	269028 8
Centre offset L_3	11.5 mm
Overhang L_1	48 mm
Standard	DIN 8024
Overall length L	180 mm
suitable indexable insert	SC.. 09T3..
Shank $\varnothing D_s$	16 mm
Minimum pre-drill $\varnothing D_{min}$	20 mm
Clamping height L_2	15 mm
Setting angle κ	45 degrees
ISO code toolholder	A16Q SSSCR/L09
Application type	right-hand
Boring depth up to	3×D
Shank type	Steel
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/260722-16/09>
