



ECO knurl forming tool set, Shank size: 12mm



Order data

Order number	290050 12
GTIN	4030741082870
Item class	29H

Description

Content:

- 1 pc. each eco knurl forming tool No. 290036 and No. 290039: Size 12
- 3 pc. knurl No. 290161: Size 15×4/0.6
- 2 pc. knurl No. 290161: Size 15×4/0.8
- 1 pc. each knurl No. 290176 and No. 290181: Size 15×4/0.6; 15×4/0.8; 15×4/1.0
- 2 pcs. roller pin No. 299911: Size 4
- 1 pc. roller pin No. 299911: Size 2

Technical description

Cutting direction	left-hand and right-hand
for knurl profile	RBL 2×BR
for knurl profile	RBR 2×BL
for knurl profile	RBL 1×BR
for knurl profile	RAA 2×AA
for knurl profile	RBR 1×BL

Data sheet

for knurl profile	RBR 1×BL
for knurl profile	RGE30° 1×GV30°
for knurl profile	RBL 1×BR
for knurl profile	RAA 1×AA
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool