

Garant**Boring bar holder slotted, HSK-T 63, Clamping Ø D1: 32mm****Order data**

Order number	318831 32
GTIN	4069515004985
Item class	31G

Description**Version:**

GARANT - more stability and vibration damping effect due to wrapping around the boring bar.

Application:

For mounting boring bars.

For use on lathes and milling centres.

Technical description

Overhang dimension A	105 mm
L ₁	80 mm
External Ø D	65 mm
Clamping Ø D ₁	32 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Side lock arbor