


**KUB Pentron® indexable drill ABS® shank, 4×D, Ø DC: 32mm**

**Order data**

Order number	236603 32
GTIN	4047109200739
Item class	24P

**Description**
**Version:**
**Bore tolerance:** D – 0.1 / + 0.3

**Application:**

With indexable inserts No. 236605 – 236610.

**Note:**

- **For use only under stable machining conditions.**
- **Version 2×D and 3×D with ABS® shank available on request.**
- **Offset-axis drilling up to  $V_{max} = 0.25$  mm.**
- **Maximum  $\varnothing = D + 0.5$  mm achievable by offsetting.**
- **Version with PSC shank available on request.**

**Technical description**

ABS® shank $\varnothing D_s$	63 mm
Reach $L_1$	128 mm
Number of cutting edges Z	1
ISO code indexable insert	SOGX 100408 32-...
Pack of insert screws	239652 15IP1 (2.8 Nm)
Series	KUB Pentron®
Nominal $\varnothing D$	32
Overhang $L_A$	167 mm
Drill depth for indexable insert drill up to	4×D

Shank	ABS
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 2,8 N·m	211750 2,8
Torx Plus® insert screw set10 pieces Drive 15IP	239652 15IP
Torx Plus® insert screw set10 pieces Drive 15IP1	239652 15IP1