



## Radius indexable insert 12° HSS-Co5, H7, Radius: R8mm



### Order data

Order number	240030 R8
GTIN	2050001099457
Item class	29W

### Description

**Version:**

Ground all round and each with four radii of the same size. The cutting edges are relief ground and have chip breakers for best cutting conditions over the entire radius sector.

The **rake angle** of 12° is suitable for general purpose use.

**Application:**

For turning convex radii on external or internal diameters.

### Technical description

Radius R <sub>1</sub>	R8
Tool material	HSS Co 5
Type of product	Cutter insert for turning