



## ER collet with seal, ER 16, Nominal clamping Ø d: 10mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 308907 10     |
| GTIN         | 4054631188558 |
| Item class   | 39Y           |

### Description

**Version:**

Through hardened and ground.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces. Metallic sealed.

**Description:**

Coolant pressure: Can be used up to 120 bar.

**Advantage:**

The coating increases the service life of the collet and ensures full functionality and precision.

**Note:**

With **seal** for through-coolant only the nominal size can be clamped. **Similar to** ISO 15488-A.

### Technical description

|                  |             |
|------------------|-------------|
| Adapter          | ER 16       |
| Standard         | ISO 15488-A |
| Concentricity    | ≤ 5 µm      |
| Type             | 425 E       |
| External Ø D     | 16.7 mm     |
| Overall length L | 27.5 mm     |

Type of product

Collet