



## ER collet with seal, ER 25, Nominal clamping Ø d: 9mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 308947 9      |
| GTIN         | 4054631126086 |
| Item class   | 39Y           |

### Description

#### Version:

Through hardened and ground.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces. Metallic sealed.

#### Description:

Coolant pressure: Can be used up to 120 bar.

#### Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

#### Note:

With **seal** for through-coolant only the nominal size can be clamped. **Similar to** ISO 15488-A.

### Technical description

|                  |             |
|------------------|-------------|
| Adapter          | ER 25       |
| Standard         | ISO 15488-B |
| Concentricity    | ≤ 5 µm      |
| Type             | 429 E       |
| External Ø D     | 25.7 mm     |
| Overall length L | 34 mm       |

Type of product

Collet