



## ER collet with seal, ER 32, Nominal clamping Ø d: 10mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 308987 10     |
| GTIN         | 4054631125973 |
| Item class   | 39Y           |

### Description

**Version:**

Through hardened and ground.

**Corrosion protection:** Collets fully coated with FAHRION Protect, including the functional faces. Metallic sealed.

**Description:**

Coolant pressure: Can be used up to 120 bar.

**Advantage:**

The coating increases the service life of the collet and ensures full functionality and precision.

**Note:**

With **seal** for through-coolant only the nominal size can be clamped. **Similar to** ISO 15488-A.

### Technical description

|               |             |
|---------------|-------------|
| Adapter       | ER 32       |
| Standard      | ISO 15488-B |
| Concentricity | ≤ 5 µm      |
| Type          | 469 E       |

## Data sheet

|                  |         |
|------------------|---------|
| External Ø D     | 32.7 mm |
| Overall length L | 40 mm   |
| Type of product  | Collet  |