

**ER collet with seal, ER 40, Nominal clamping Ø d: 12mm****Order data**

Order number	308993 12
GTIN	4054631126482
Item class	39Y

Description**Version:**

Through hardened and ground.

Corrosion protection: Collets fully coated with FAHRION Protect, including the functional faces. Metallic sealed.

Description:

Coolant pressure: Can be used up to 120 bar.

Advantage:

The coating increases the service life of the collet and ensures full functionality and precision.

Note:

With **seal** for through-coolant only the nominal size can be clamped. **Similar to** ISO 15488-A.

Technical description

Adapter	ER 40
Standard	ISO 15488-B
Concentricity	≤ 5 µm
Type	471 E
External Ø D	40.7 mm
Overall length L	46 mm

Type of product

Collet