


**KOMET® recessing bar Form f, Type: B03**

**Order data**

Order number	240078 B03
GTIN	4047109004030
Item class	24H

**Description**
**Version:**

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L = extended shank.**

**Tool material:**

**HSS/Co10** – for difficult to machine materials.

**Note:**

**For suitable boring bar holders see No. 240070 and No. 240072.**

Tool material: HSS Co 10

Boring depth: 26 mm

for bores from Ø: 7 mm

Overall length: 65 mm

Shank Ø: 8 mm

**Technical description**

Boring depth	26 mm
for bores from Ø	7 mm
Type	B03
Overall length	65 mm
Shank Ø	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

