

Garant**Digital workshop caliper HCT IP67 with measuring tips, Measuring range: 300mm****Order data**

Order number	415371 300
GTIN	4069515008167
Item class	41A

Description**Version:**

Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app (available free of charge for Android and iOS) and the HCT Windows app (available for Windows). Can also be used via a Human Interface Device (HID).

Digital workshop caliper IP67. **Easy-to-read, high-contrast LCD display with 11.5mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene® surface**. The measuring faces are precision-lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 1 batteries No. 081560 size CR2032.

Spare part:

Battery holder No. 412237 size B.

Technical description

Reversible reading	mm / inch
#Article no of the battery / rechargeable battery fitted	081560 CR2032
#Number of batteries contained	1

Measurement deviation E MPE	±0.03 mm
Standard	ISO 13385
Scale divisions	0.01 mm
Digit height LCD display	11.5 mm
Battery type	Button cell
Internal jaw Ø	10 mm
Power supply	Battery-powered
Scale divisions	0.0005 in
Calibration	A1
Measuring range	0 - 300 mm
Wireless application	HID (Human Interface Device)
Wireless application	HCT mobile app
Wireless application	HCT Windows app
Jaw length	100 mm
IP Index of Protection	IP 67
Series	HCT
Auto switch-off	yes
Packaging	sturdy box
Interface	Bluetooth® interface
Measuring tips	yes
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop caliper

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/415371-300>