

Garant**Digital workshop caliper IP67 without measuring tips, Measuring range: 300mm****Order data**

Order number	415372 300
GTIN	4069515008198
Item class	41A

Description**Version:**

Digital workshop caliper IP67. **Easy-to-read, high-contrast LCD display with 11.5mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene® surface**. The measuring faces are precision-lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 1 batteries No. 081560 size CR2032.

Spare part:

Battery holder No. 412237 size B.

Technical description

Standard	ISO 13385
#Number of batteries contained	1
Reversible reading	mm / inch
Auto switch-off	yes
Jaw length	100 mm

Data sheet

Scale divisions	0.01 mm
Internal jaw Ø	10 mm
IP Index of Protection	IP 67
Calibration	A1
Scale divisions	0.0005 in
Power supply	Battery-powered
Measuring range	0 - 300 mm
#Article no of the battery / rechargeable battery fitted	081560 CR2032
Measurement deviation E MPE	±0.03 mm
Digit height LCD display	11.5 mm
Battery type	Button cell
Packaging	sturdy box
Interface	Digimatic interface
Interface	USB interface
Measuring tips	no
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop caliper

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/415372-300>