


KOMET® recessing bar Form f, Type: B03L

Order data

Order number	240078 B03L
GTIN	4047109017498
Item class	24H

Description
Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Tool material: HSS Co 10

Boring depth: 26 mm

for bores from \varnothing : 7 mm

Overall length: 125 mm

Shank \varnothing : 8 mm

Technical description

Type	B03L
Overall length	125 mm
Boring depth	26 mm
for bores from \varnothing	7 mm
Shank \varnothing	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

