

 KOMET

KOMET® internal thread boring bar, right-hand Form 60° (metric), Type: B03

Order data

Order number	240084 B03
GTIN	4047109016934
Item class	24H

Description
Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Technical description

for bores from Ø	7 mm
for pitches up to	1.5 mm
Type	B03
Boring depth	26 mm
Overall length	65 mm
Shank Ø	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning