

Garant**Eco toolholder axial single, right-hand, HSK-T 63, for toolholder square: 25mm****Order data**

Order number	318622 25
GTIN	4069515009010
Item class	31G

Description**Version:**

With adjustable cooling nozzle with internal thread.

GARANT - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT Eco.

Slim contour for better accessibility.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

With pass-through shim. Suitable for toolholders with shank 20 **and** 25 mm.

Technical description

Overhang dimension A	130 mm
for toolholder square	25 mm
Clamping length L ₁	88 mm
B	25 mm
External Ø D	78 mm

Data sheet

Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Arbor