

 KOMET

KOMET® roughing bar Form g, Type: B01

Order data

Order number	240074 B01
GTIN	4047109016415
Item class	24H

Description
Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Tool material: HSS Co 10

Boring depth: 20 mm

for bores from \varnothing : 3 mm

Overall length: 60 mm

Shank \varnothing : 8 mm

Technical description

Boring depth	20 mm
for bores from \varnothing	3 mm
Overall length	60 mm
Type	B01
Shank \varnothing	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

