



KOMET® recessing bar Form f, Type: B05



Order data

Order number	240078 B05
GTIN	4047109016316
Item class	24H

Description

Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Tool material: HSS Co 10

Boring depth: 50 mm

for bores from Ø: 12 mm

Overall length: 80 mm

Shank Ø: 8 mm

Technical description

for bores from Ø	12 mm
Overall length	80 mm
Boring depth	50 mm
Type	B05
Shank Ø	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

