

 KOMET

KOMET® roughing bar Form g, Type: B02

Order data

Order number	240074 B02
GTIN	4047109016453
Item class	24H

Description
Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Tool material: HSS Co 10

Boring depth: 24 mm

for bores from \varnothing : 5 mm

Overall length: 60 mm

Shank \varnothing : 8 mm

Technical description

for bores from \varnothing	5 mm
Boring depth	24 mm
Type	B02
Overall length	60 mm
Shank \varnothing	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

