

**LED torch C series, Type: C5R****Order data**

Order number	081447 C5R
GTIN	4058205038348
Item class	04B

**Description****Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Including 1 pc. Li-ion rechargeable battery type 14500 3.7 V, 1 pc. Floating Charge System, 1 pc. hand loop, 1 pc. voucher for belt bag.

**Note:**

**2+5-year warranty upon registration on [www.ledlenser.com](http://www.ledlenser.com).**

Unless otherwise specified below, we provide a manufacturer's warranty on our products of

- **seven years if the product is registered online within 12 weeks from the date of purchase**
- **two years if the product is not registered online or is not registered online in a timely manner; we also grant a warranty period of two years (without extension of the warranty period, no registration), calculated from the date of purchase for proper functioning of rechargeable batteries, the Powercase and the battery box.**

**Technical description**

IP Index of Protection	IP 54
Type of rechargeable battery	Lithium-ion
CRI value	75
Colour of housing	BLACK
Battery voltage	3.7 V
Rapid Focus	yes

## Data sheet

Illumination	20 - 420 lm
Power supply	Battery-powered
Illumination time stage 2	3 h
Illumination range	50 - 240 m
Illumination time	3 - 15 h
Bulb	LED module
Illumination step 2	420 lm
Advanced Focus System (AFS)	yes
Light colour	cold white
Manufacturer's designation	C5R
Overall length	117 mm
International size	14500
Series	C series
Number of rechargeable batteries contained	1
Including belt pocket	yes
Battery capacity	0.7 Ah
Replaceable battery	yes
Weight	75 g
Head Ø	26 mm
Type of product	Torch

### Suitable products

No Shop URL available for: 081447 C5R